

SSI Technologies, Inc.
CONTROLS TECHNOLOGIES DIVISION

SSI Technologies, Inc.

SSI Technologies,
- CONTROLS TECHNOLOGIES DIV

P51-75-G-Y-P-5V-000-000

Nambari ya Sehemu:	P51-75-G-Y-P-5V-000-000
Mtengenezaji / Brand:	SSI Technologies, Inc.
Maelezo ya bidhaa	SENSOR 75PSI 7/16-20-2B 1-5V
Datasheets:	1.P51-75-G-Y-P-5V-000-000.pdf 2.P51-75-G-Y-P-5V-000-000.pdf
Hali ya RoHs	Kuongoza bure / RoHS Inavyotakiwa
Hali	720 pcs stock
Meli Kutoka	Hong Kong
Njia ya Uhamisho	DHL/Fedex/TNT/UPS/EMS

OMBI LA NUKUU

Picha inaweza kuwa uwakilishi. Angalia maelezo ya maelezo ya bidhaa.

Ufafanuzi wa P51-75-G-Y-P-5V-000-000

NAMBARI YA SEHEMU	P51-75-G-Y-P-5V-000-000
MTENGENEZAJI	SSI Technologies, Inc.
MAELEZO	SENSOR 75PSI 7/16-20-2B 1-5V
HALI YA BURE YA BURE / HALI YA ROHS	Kuongoza bure / RoHS Inavyotakiwa
KIASI INAPATIKANA	720 pcs
KARATASI YA DATA	1.P51-75-G-Y-P-5V-000-000.pdf 2.P51-75-G-Y-P-5V-000-000.pdf
UGAVI WA VOLTAGE	8 V ~ 30 V
SINEMA YA KUKOMESHA	Packard, 3 Pin
DUKA LA KIFAA CHA WASAMBAZAJI	-
MFULULIZO	MediaSensor™
AINA YA SHINIKIZO	Vented Gauge
SINEMA YA PORT	Threaded
UKUBWA WA BANDARI	Female - 7/16" (11.11mm) UNF
PAKET / UCHUNGUZI	Cylinder
AINA YA PATO	Analog Voltage
PATO	1 V ~ 5 V
MAJINA MENGINE	P51-75-G-Y-P-5V P51-75-G-Y-P-5V-ND
JOTO LA UENDESHAJI	-40°C ~ 105°C
SHINIKIZO LA UENDESHAJI	75 PSI (517.11 kPa)
KIWANGO CHA SENSITIVITY MOISTURE (MSL)	1 (Unlimited)
UPEO WA UPEO	-
HALI YA BURE YA BURE / HALI YA ROHS	Lead free / RoHS Compliant
VIPENGELE	Amplified Output, Temperature Compensated
MAELEZO YA KINA	Pressure Sensor 75 PSI (517.11 kPa) Vented Gauge Female - 7/16" (11.11mm) UNF 1 V ~ 5 V Cylinder
USAHIHI	±0.5%

Tags kuhusiana

SSI Technologies, Inc. P51-75-G-Y-P-5V-000-000	Mgawanyiko wa P51-75-G-Y-P-5V-000-000	Mtoa P51-75-G-Y-P-5V-000-000
P51-75-G-Y-P-5V-000-000 Bei	P51-75-G-Y-P-5V-000-000 Picha	P51-75-G-Y-P-5V-000-000 Image
Datasheet ya P51-75-G-Y-P-5V-000-000 PDF	P51-75-G-Y-P-5V-000-000 Pakua Datasheet	Datasheet ya P51-75-G-Y-P-5V-000-000
P51-75-G-Y-P-5V-000-000 Stock	Nunua P51-75-G-Y-P-5V-000-000	Nunua SSI Technologies, Inc. P51-75-G-Y-P-5V-000-000
SSI Technologies, Inc. P51-75-G-Y-P-5V-000-000	Mtoa SSI Technologies, Inc.	Mgawanyiko wa SSI Technologies, Inc.
SSI Technologies, Inc. P51-75-G-Y-P-5V-000-000	SSI Technologies Inc P51-75-G-Y-P-5V-000-000	

Bidhaa zinazohusiana

<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Y-MD-4.50VP-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 7/16-20-2B .5-4.5V</p> <p>Katika hisa: 780 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Z-D-20MA-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 1/4-18NPT 4-20MA</p> <p>Katika hisa: 520 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Y-P-4.50VP-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 7/16-20-2B .5-4.5V</p> <p>Katika hisa: 739 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Z-D-4.50VP-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 1/4-18NPT .5-4.5V</p> <p>Katika hisa: 545 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Z-I12-20MA-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 1/4-18NPT 4-20MA</p> <p>Katika hisa: 491 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Y-MD-4.5V-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 7/16-20-2B .5-4.5V</p> <p>Katika hisa: 718 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Z-D-4.5V-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 1/4-18NPT .5-4.5V</p> <p>Katika hisa: 472 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Y-P-4.5V-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 7/16-20-2B .5-4.5V</p> <p>Katika hisa: 689 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Y-P-20MA-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 7/16-20-2B 4-20MA</p> <p>Katika hisa: 754 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Z-I12-4.50VP-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 1/4-18NPT .5-4.5V</p> <p>Katika hisa: 514 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>
<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Y-MD-5V-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 7/16-20-2B 1-5V</p> <p>Katika hisa: 722 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>	<div style="border: 1px solid #ccc; padding: 5px;"> <p>P51-75-G-Z-D-5V-000-000</p> <p>Wazalishaji: SSI Technologies, Inc.</p> <p>Maelezo: SENSOR 75PSI 1/4-18NPT 1-5V</p> <p>Katika hisa: 539 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; width: fit-content; margin: 0 auto;">RFQ</p> </div>