

Advanced Photonix (Luna

Optoelectronics)

PDB-V607-1

Nambari ya Sehemu:	PDB-V607-1
Mtengenezaji / Brand:	Advanced Photonix (Luna Optoelectronics)
Maelezo ya bidhaa	PHOTODIODE BLUE 14.5MM SQ BARE
Datasheets:	PDB-V607-1.pdf
Hali ya RoHS	Ina lead / RoHS isiyo ya kuzingatia
Hali	6409 pcs stock
Meli Kutoka	Hong Kong
Njia ya Uhamisho	DHL/Fedex/TNT/UPS/EMS

OMBI LA NUKUU

Picha inaweza kuwa uwakilishi. Angalia maelezo ya maelezo ya bidhaa.

Ufafanuzi wa PDB-V607-1

NAMBARI YA SEHEMU	PDB-V607-1
MTENGENEZAJI	Advanced Photonix (Luna Optoelectronics)
MAELEZO	PHOTODIODE BLUE 14.5MM SQ BARE
HALI YA BURE YA BURE / HALI YA ROHS	Ina lead / RoHS isiyo ya kuzingatia
KIASI INAPATIKANA	6409 pcs
KARATASI YA DATA	PDB-V607-1.pdf
WAVELENGTH	940nm
VOLTAGE - DC REVERSE (VR) (MAX)	25V
KUANGALIA ANGLE	-
MTAZAMO WA SPECTRAL	350nm ~ 1100nm
MFULULIZO	-
MSIKIVU @ NM	-
MUDA WA KUJIBU	1μs
UFUNGAJI	Tray
PAKET / UCHUNGUZI	Die
MAJINA MENGINE	PT-PDB-V607-1
JOTO LA UENDESHAJI	-40°C ~ 100°C
AINA YA KUINUA	Free Hanging
KIWANGO CHA SENSITIVITY MOISTURE (MSL)	1 (Unlimited)
HALI YA BURE YA BURE / HALI YA ROHS	Contains lead / RoHS non-compliant
AINA YA DIODE	-
MAELEZO YA KINA	Photodiode 940nm 1μs Die
SASA - GIZA (AINA)	25nA
RANGI - INAIMARISHWA	Blue
ENEO LA KAZI	14.5mm ²

Tags kuhusiana

Advanced Photonix (Luna Optoelectronics) PDB-V607-1	Mgawanyiko wa PDB-V607-1	Mtoa PDB-V607-1
PDB-V607-1 Bei	PDB-V607-1 Picha	PDB-V607-1 Image
Datasheet ya PDB-V607-1 PDF	PDB-V607-1 Pakua Datasheet	Datasheet ya PDB-V607-1
PDB-V607-1 Stock	Nunua PDB-V607-1	Nunua Advanced Photonix (Luna Optoelectronics) PDB-V607-1
Advanced Photonix (Luna Optoelectronics) PDB-V607-1	Mtoa Advanced Photonix (Luna Optoelectronics)	Mgawanyiko wa Advanced Photonix (Luna Optoelectronics)
Advanced Photonix (Luna Optoelectronics) PDB-V607-1	Advanced Photonix Inc PDB-V607-1	Advanced Photonix (Luna Optoelectronics) PDB-V607-1
Luna Optoelectronics PDB-V607-1		

Bidhaa zinazohusiana

<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V604-1</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 4.34MM SQ BARE</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 6557 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V607-3</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 14.5MM SQ BUSS</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 3027 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V608-2</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 38.4MM SQ PVC</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 6750 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V604-2</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 4.34MM SQ PVC</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 6715 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V604-3</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 4.34MM SQ BUSS</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 4699 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V608-3</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 38.4MM SQ BUSS</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 5226 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V605-1</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 10.84MM SQ BARE</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 4850 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V609-1</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 42.4MM SQ BARE</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 4934 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V607-2</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 14.5MM SQ PVC</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 4335 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V608-1</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 38.4MM SQ BARE</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 6416 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>
<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V605-3</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 10.84MM SQ BUSS</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 6867 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>	<div style="display: flex; align-items: center;"> <div> <p style="margin: 0;">PDB-V605-2</p> <p style="margin: 0; font-size: 0.8em;">Wazalishaji: Advanced Photonix (Luna Optoelectronics)</p> <p style="margin: 0; font-size: 0.8em;">Maelezo: PHOTODIODE BLUE 10.84MM SQ PVC</p> <p style="margin: 0; font-size: 0.8em;">Katika hisa: 5979 pcs</p> <p style="text-align: center; background-color: #ccc; padding: 2px; margin-top: 5px; font-weight: bold; font-size: 0.8em;">RFQ</p> </div> </div>